



MADE IN BRITAIN

Disabled Toilet Call



Supporting our
NHS



STATIC
SYSTEMS
GROUP

Disabled Toilet Call

Static Systems' Disabled Toilet Call system is fully compliant with BS 8300: 2018, easy to install, reliable and simple to use.

Disabled Toilet Call systems - comprising an alarm pull cord with two red bangles and a reset button - are recommended for use within all new public buildings; for use by wheel chair users, ambulant disabled people, people with small babies and children, and people encumbered by luggage.

The pull cord should be reachable from changing or shower seats, from the WC and from the floor. An alarm reset button should be positioned on the wall adjacent to the WC, the shower seat or changing seat.

A pull cord and alarm reset button should also be provided near to all seating where a transfer procedure might be carried out, and the pull cord should be not more than 50mm from the adjacent wall.

At a glance:-

- Fully independent, standalone solution*
- BS 8300 compliant
- Separate power supply in metal enclosure
- Powerful LEDs and sounder
- Up to 3 pull cords can be connected to the Controller Unit

Flash and Tone Patterns:-

Alarm Type:	Toilet Call
Flash Pattern:	Steady
Tone Pattern:	1 second on, 3 seconds off
Over Door Lamp:	Orange
Reset Location:	Origin of call

* Integrated disabled toilet call systems providing event logging and notification as part of the nurse call system in accordance with HTM 08-03 also available.

Equipment Specification

Toilet Call Pull Cord Unit with Reassurance

Part Code:	75847W
Facilities:	<ul style="list-style-type: none">• Reassurance LED• 3 Metre Plastic Cord (red)• 2 Pull Handles (red)
Plate Size:	86mm x 86mm
Box Size:	Flush (Ceiling Mounted) – BS 1 Gang (Part Code: 39100) Surface (Ceiling Mounted) – 96mm x 85mm x 30mm (Part Code: 39322)
Material:	ABS Plastic
Finish:	Fine Spark Textured, White

To assist in the fight against bacteria such as MRSA, pull cord units include a wipe-clean, anti-microbial cord and pull. Units are designed to comply with HTM 08-03: Bedhead Services and with BS 8300-2: 2018 (Section 13.7.2) for use in public access WCs.

Toilet Call Pull Cord Unit with Reassurance - Splashproof

Part Code:	75848W
Facilities:	<ul style="list-style-type: none">• Reassurance LED• 3 Metre Plastic Cord (red)• 2 Pull Handles (red)
Plate Size:	86mm x 86mm
Ingress Protection:	IP65
Box Size:	Flush (Ceiling Mounted) – BS 1 Gang (Part Code: 39100) Surface (Ceiling Mounted) – 96mm x 85mm x 30mm (Part Code: 39322)
Material:	ABS Plastic
Finish:	Fine Spark Textured, White

Reset Unit

Part Code:	75710W
Facilities:	<ul style="list-style-type: none">• Reset Push
Plate Size:	146mm x 86mm
Box Size:	Flush – 2 Gang (Part Code: 39101) Surface – 2 Gang (Part Code: 39301B)
Material:	1.5mm Steel
Finish:	Powder Coated Pure White RAL 9010, 25% gloss (matt)

Toilet Call Lamp and Tone Unit

Part Code:	75817W
Facilities:	<ul style="list-style-type: none">• One Way LED (orange)• Tone Loudspeaker Module• Protective Grill
Plate Size:	166mm x 91mm
Box Size:	Flush – 150mm x 75mm x 50mm (Part Code: 39125) Surface – 168mm x 93mm x 52mm (Part Code: 39339)
Material:	1.5mm Steel
Finish:	Powder Coated Pure White RAL 9010, 25% gloss (matt)

Note: This unit is supplied with a pre-programmed control node.

Toilet Call Power Supply Unit


Part Code:	75807
Output:	24 Volts dc Switchmode Power Supply Unit (1 Amp)
Plate Size:	249 mm x 279mm
Box Size:	Surface – 250mm x 280mm x 53mm (Part Code: 39151W)
Material:	1.5mm Steel
Finish:	Powder Coated Pure White RAL 9010, 25% gloss (matt)

Note: This unit includes space for an expansion node.

Connection

Toilet Call Power Supply Unit (Part Code: 75807)

Note: This unit requires a 230V ac mains supply which should be derived from a suitable UPS to ensure continuity of supply during changeover from normal to standby/generator supply. Full battery backed units and UPS units are available at additional cost.



Toilet Call Pull Cord Unit with Reassurance (Part Code: 75847W or 75848W)

Requires Back Box (Part Code: 39100)

Toilet Call Lamp and Tone Unit (Part Code: 75817W)

Requires Back Box (Part Code: 39125)

Reset Unit (Part Code: 75710W)

Requires Back Box (Part Code: 39101)

The complete family of advanced nurse call solutions.



Aspire smart_{sync}[®] / Wireless solution



Codemlon[™] / Addressable loop wired solution



Ultima[™] / Full end-to-end, open protocol IP solution



STATIC
SYSTEMS
GROUP

www.staticsystems.co.uk

Static Systems Group PLC
Heath Mill Road, Wombourne, Staffordshire, WV5 8AN, UK.
T: +44 (0) 1902 895 551

In line with our company policy of continuous product development, we reserve the right to change design and improve specification without prior notice.



Follow us on Twitter
[@static_systems](https://twitter.com/static_systems)

FOCUS 005 (08/2020)