



RELIABLE - QUIET - EASY TO USE

Quattro

Bedpan Disposal System

With proven reliability, easy to clean surfaces, classleading quietness and efficiency, the **Quattro** by Haigh has been designed with Nurses, Estate Managers and Site Operators front of mind



Reliable. For lower running costs.

We absolutely understand that your bedpan machine must work without fail tens, if not hundreds of times per day in a busy sluice-room.

Quattro is tested on pulp disposable items from all of the many manufacturers and types of product, from urine bottles to large wash-bowls and sample pots

Haigh test all machines rigorously as they leave our production line. Many features have been expertly built in specifically to reduce the risk of machine failure or blockage of your drainage system:

- ✓ Weir technology controls particle size
- ✓ Automatic and mechanical operation
- ✓ Ease of access on all key components

Foreign objects (gloves etc.) are held back in the **Quattro**, macerated pulp particle size is also regulated by our unique concentric weir technology, controlling particle size and protecting drains from blockage.

FAST, QUIET, CLEAN, EASY
SUPERFINE MACERATION

PROTECT YOUR DRAINS

QUALITY ASSURED ON ALL TYPES OF PULP

Compliant. Best practice.

Your sluice room may not be the most glamorous part of your site but it need not be unpleasant to work in and needs to enable compliant with relevant regulations.

Quattro improves your site environment:

- ✓ Easy to clean
- ✓ Embedded antimicrobial silver ions
- ✓ Efficient use of Energy and Water for ISO I 400 I
- ✓ Quality lid seal restricts odours
- ✓ End of cycle sanitization
- ✓ WRAS approved

Cleaner surfaces combined with the single use pulp concept demonstrably leads to lower risk of cross infection.



Easy to Use

Quattro is designed to make the life of the user as straightforward and pleasant as possible. As the 5th generation of the Haigh Sluicemaster range **Quattro** does this by giving you:

- ✓ The lowest loading height
- ✓ The deepest opening
- ✓ High visibility foot pedal opening
- ✓ Automatic starting
- ✓ Fast cycle time
- The quietest macerator as tested by Quietmark

As a result, not only does **Quattro** aim make the life of the carer better but particularly with its class-leading low sound levels and short run time, the disposal of patient waste is kept discrete with minimal disruption, even during the night.

Traditional 75mm macerator dump valve size

Typical 2"/ 50mm drain pipe 